Eaton FRN-R-30

Catalog Number: FRN-R-30

Eaton Bussmann series FRN-R fuse, 30 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 8 sec at 500%, 20 kAIC at 125 Vdc|200 kAIC at 250 V, Standard, 250 V, 125 Vdc

General specifications

Product Name

Eaton Bussmann series FRN-R fuse

UPC

051712101769

Product Height

0.81 in

Product Weight

1.95 lb

Compliances
CE Marked

Catalog Number

FRN-R-30

Product Length/Depth

3 in

Product Width

0.81 in

Warranty

Not Applicable



Electrical rating

Amperage Rating

30 A

Interrupt rating

200 kAIC at 250 Vac 20 kAIC at 125 Vdc

Response time

8 sec at 500%

Voltage rating

250 Vac, 125 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Special features

Finger safe

Resources

Catalogs

Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FRN-R-30

Technical data sheets

FRN-R-30~FUSETRON DUAL-ELEMENT CLASS RK5

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia