

# Eaton FRN-R-400

Catalog Number: FRN-R-400

Eaton Bussmann series FRN-R fuse, 400 A, Dual, Class RK5, Non-indicating, Blade end x blade end, 10 sec at 500%, 20 kAIC at 125 Vdc|200 kAIC at 250 V, Standard, 250 V, 125 Vdc

## General specifications

Product Name	Catalog Number
Eaton Bussmann series FRN-R fuse	FRN-R-400
UPC	EAN
051712507530	5027590060813
Product Length/Depth	Product Height
8.63 in	2.06 in
Product Width	Product Weight
2.06 in	1.6 lb
Warranty	Compliances
Not Applicable	CE Marked



## Electrical rating

### Amperage Rating

400 A

### Interrupt rating

200 kAIC at 250 Vac

20 kAIC at 125 Vdc

### Response time

10 sec at 500%

### Voltage rating

250 Vac, 125 Vdc

## Physical details

### Number of elements

Dual

### Packaging type

Standard

## General information

### Class

Class RK5

### Connection

Blade end x blade end

### Fuse indicator

Non-indicating

### Special features

Finger safe

## Resources

### Catalogs

[Bussmann series complete full line catalog no. 1007](#)

[Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses](#)

### Multimedia

[Bussmann series Fuseology](#)

### Specifications and datasheets

[Eaton Specification Sheet - FRN-R-400](#)

### Technical data sheets

[FRN-R-400~FUSETRON DUAL-ELEMENT CLASS RK5](#)

### Technical service bulletins

[Datasheet - FNQ-30](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com  
© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)