# Eaton FRN-R-600

# Catalog Number: FRN-R-600

Eaton Bussmann series FRN-R fuse, 600 A, Dual, Class RK5, Non-indicating, Blade end x blade end, 10 sec at 500%, 20 kAIC at 125 Vdc|200 kAIC at 250 V, Standard, 250 V, 125 Vdc

## General specifications



Eaton Bussmann series FRN-R fuse

UPC

051712507561

**Product Height** 

0.81 in

**Product Weight** 

0.11 lb

Compliances

**CE Marked** 

Catalog Number

FRN-R-600

Product Length/Depth

3 in

**Product Width** 

0.81 in

Warranty

Not Applicable



### Electrical rating

Amperage Rating

600 A

Interrupt rating

20 kAIC at 125 Vdc 200 kAIC at 250 Vac

Response time

10 sec at 500%

Voltage rating

250 Vac, 125 Vdc

#### Physical details

Number of elements

Dual

Packaging type

Standard

#### General information

Class

Class RK5

Connection

Blade end x blade end

Fuse indicator

Non-indicating

#### Resources

#### Catalogs

Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses

Bussmann series complete full line catalog no. 1007

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FRN-R-600

Technical data sheets

FRN-R-600~FUSETRON DUAL-ELEMENT

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia