

Eaton FRN-R-6-1/4

Catalog Number: FRN-R-6-1/4

Eaton Bussmann series FRN-R fuse, 6.25 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 8 sec at 500%, 20 kAIC at 125 Vdc|200 kAIC at 250 V, Standard, 250 V, 125 Vdc

General specifications

Product Name	Catalog Number
Eaton Bussmann series FRN-R fuse	FRN-R-6-1/4
UPC	Product Length/Depth
051712507240	3 in
Product Height	Product Width
0.81 in	0.81 in
Product Weight	Warranty
0.32 lb	Not Applicable
Compliances	
CE Marked	

Electrical rating

Amperage Rating

6.25A

Interrupt rating

20 kAIC at 125 Vdc

200 kAIC at 250 Vac

Response time

8 sec at 500%

Voltage rating

250 Vac, 125 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Resources

Catalogs

[Bussmann series complete full line catalog no. 1007](#)

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - FRN-R-6-1/4](#)

Technical data sheets

[FRN-R-6-1/4~FRN-R-6-1-4~FUSETRON DUAL-ELEMENT CLASS RK5](#)