

## Eaton Bussmann series FRS-R fuse

### FRS-R-100

UPC:051712508438

#### Dimensions:

- **Height:** .81 IN
- **Length:** 5 IN
- **Width:** .81 IN

**Weight:**.4 LB

#### Warranties:

- Not Applicable

#### Specifications:

- **Type:** Current-limiting, time delay
- **Application:** Combination starters, motor control centers, machinery disconnects, power panelboards
- **Voltage Rating:** 600 Vac, 300 Vdc
- **Amperage Rating:** 100A
- **Interrupt Rating:** 200 kAIC at 600 Vac, 20 kAIC at 300 Vdc
- **Class:** Class RK5
- **Connection:** Blade end X blade end
- **Packaging Type:** Standard
- **Diameter:** 1.11 IN
- **Fuse Indicator:** Non Indicating
- **Response Time:** 10s at 500%
- **Number Of Elements:** Dual

#### Supporting documents:

- [Product Catalog](#)
- [FUSETRON DUAL ELEMENT FUSE cLASS RK5](#)
- [Product Datasheet](#)

**Certifications:** No Data

**Product compliance:**

- CE Marked

---

© 2016 Eaton. All rights reserved.