Eaton FRS-R-125

Catalog Number: FRS-R-125

Eaton Bussmann series FRS-R fuse, 125 A, Dual, Class RK5, Non-indicating, Blade end x blade end, 10 sec at 500%, 200 kAIC at 600 V|20 kAIC at 300 Vdc, Standard, 600 V, 300 Vdc

General specifications

Product Name

Eaton Bussmann series FRS-R fuse

UPC

051712508452

Product Height

0.81 in

Product Weight

0.4 lb

Compliances

CE Marked

Catalog Number

FRS-R-125

Product Length/Depth

5 in

Product Width

0.81 in

Warranty

Not Applicable





Electrical rating

Amperage Rating

125 A

Interrupt rating

200 kAIC at 600 Vac 20 kAIC at 300 Vdc

Response time

10 sec at 500%

Voltage rating

600 Vac, 300 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection

Blade end x blade end

Fuse indicator

Non-indicating

Resources

Catalogs

Bussmann series complete full line catalog no. 1007

Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FRS-R-125

Technical data sheets

FRS-R-125~FUSETRON DUAL ELEMENT FUSE CLASS RK5

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia