Eaton FRS-R-15

Catalog Number: FRS-R-15

Eaton Bussmann series FRS-R fuse, 15 A, Dual, Class RK5, Nonindicating, Ferrule end x ferrule end, 10 sec at 500%, 20 kAIC at 300 Vdc|200 kAIC at 600 V, Standard, 600 V, 300 Vdc

General specifications

Product Name Eaton Bussmann series FRS-R fuse

UPC 051712508308

Product Height 0.81 in

Product Weight 0.15 lb

Compliances CE Marked Catalog Number FRS-R-15

Product Length/Depth 5 in

Product Width 0.81 in

Warranty

Not Applicable





Electrical rating

Amperage Rating

15 A

Interrupt rating 200 kAIC at 600 Vac

20 kAIC at 300 Vdc

Response time 10 sec at 500%

Voltage rating 600 Vac, 300 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection Ferrule end x ferrule end

Fuse indicator

Non-indicating

Resources

Multimedia Bussmann series Fuseology

Specifications and datasheets Eaton Specification Sheet - FRS-R-15

Technical data sheets FRS-R-15~FUSETRON DUAL ELEMENT FUSE CLASS RK5

Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia