# Eaton FRS-R-40

# Catalog Number: FRS-R-40

Eaton Bussmann series FRS-R fuse, 40 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 10 sec at 500%, 200 kAIC at 600 V|20 kAIC at 250 Vdc, Standard, 600 V, 250 Vdc

## General specifications

**Product Name** 

Eaton Bussmann series FRS-R fuse

UPC

051712508360

**Product Height** 

2.34 in

**Product Weight** 

2.25 lb

Compliances
CE Marked

Catalog Number

FRS-R-40

Product Length/Depth

11.63 in

**Product Width** 

2.34 in

Warranty

Not Applicable





#### Electrical rating

**Amperage Rating** 

40 A

Interrupt rating

200 kAIC at 600 Vac 20 kAIC at 250 Vdc

Response time

10 sec at 500%

Voltage rating

600 Vac, 250 Vdc

### Physical details

Number of elements

Dual

Packaging type

Standard

#### General information

Class

Class RK5

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

#### Resources

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FRS-R-40

Technical data sheets

FRS-R-40~FUSETRON DUAL ELEMENT FUSE CLASS RK5

Technical service bulletins

Datasheet - FNQ-30

Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.









