# Eaton FRS-R-400

# Catalog Number: FRS-R-400

Eaton Bussmann series FRS-R fuse, 400 A, Dual, Class RK5, Nonindicating, Blade end x blade end, 10 sec at 500%, 20 kAIC at 300 Vdc|200 kAIC at 600 V, Standard, 600 V, 300 Vdc

## General specifications

#### Product Name

Eaton Bussmann series FRS-R fuse

UPC 051712508537

Product Height 1.06 in

Product Weight 3 lb

Compliances CE Marked Catalog Number FRS-R-400 Product Length/Depth 5.5 in

Product Width 1.06 in

Warranty

Not Applicable





## Electrical rating

# Amperage Rating

400 A

## Interrupt rating

200 kAIC at 600 Vac 20 kAIC at 300 Vdc

## Response time 10 sec at 500%

10 360 at 500 /0

## Voltage rating

600 Vac, 300 Vdc

## Physical details

#### Number of elements

Dual

## Packaging type

Standard

## General information

Class

Class RK5

Connection Blade end x blade end

Fuse indicator

Non-indicating

## Resources

## Catalogs Bussmann series full line catalog 1007, section 01- low voltage branch circuit fuses

Bussmann series complete full line catalog no. 1007

## Multimedia

Bussmann series Fuseology

#### Specifications and datasheets

Eaton Specification Sheet - FRS-R-400

## Technical data sheets

FRS-R-400~FUSETRON DUAL ELEMENT FUSE CLASS RK5

#### Technical service bulletins

Datasheet - FNQ-30



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com © 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

Eaton.comAll other trademarks are© 2024 Eaton. All Rightsproperty of their respectiveReserved.owners.



Eaton.com/socialmedia