Eaton FRS-R-45

Catalog Number: FRS-R-45

Eaton Bussmann series FRS-R fuse, 45 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 10 sec at 500%, 20 kAIC at 250 Vdc|200 kAIC at 600 V, Standard, 600 V, 250 Vdc

General specifications

Product Name

Eaton Bussmann series FRS-R fuse

UPC

051712508377

Product Height

2.88 in

Product Weight

3.6 lb

Compliances

CE Marked

Catalog Number

FRS-R-45

Product Length/Depth

13.38 in

Product Width

2.88 in

Warranty

Not Applicable



Electrical rating

Amperage Rating

45 A

Interrupt rating

20 kAIC at 250 Vdc 200 kAIC at 600 Vac

Response time

10 sec at 500%

Voltage rating

600 Vac, 250 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Resources

Multimedia

Bussmann series Fuseology

Specifications and datasheets

Eaton Specification Sheet - FRS-R-45

Technical data sheets

FRS-R-45~FUSETRON DUAL ELEMENT FUSE CLASS RK5

Technical service bulletins

Datasheet - FNQ-30

Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.













Eaton.com/socialmedia