

Eaton FRS-R-50

Catalog Number: FRS-R-50

Eaton Bussmann series FRS-R fuse, 50 A, Dual, Class RK5, Non-indicating, Ferrule end x ferrule end, 10 sec at 500%, 20 kAIC at 250 Vdc|200 kAIC at 600 V, Standard, 600 V, 250 Vdc



General specifications

Product Name	Catalog Number
Eaton Bussmann series FRS-R fuse	FRS-R-50
UPC	Product Length/Depth
051712508384	13.38 in
Product Height	Product Width
2.88 in	2.88 in
Product Weight	Warranty
3.6 lb	Not Applicable
Compliances	
CE Marked	

Electrical rating

Amperage Rating

50 A

Interrupt rating

20 kAIC at 250 Vdc
200 kAIC at 600 Vac

Response time

10 sec at 500%

Voltage rating

600 Vac, 250 Vdc

Physical details

Number of elements

Dual

Packaging type

Standard

General information

Class

Class RK5

Connection

Ferrule end x ferrule end

Fuse indicator

Non-indicating

Resources

Multimedia

[Bussmann series Fuseology](#)

Specifications and datasheets

[Eaton Specification Sheet - FRS-R-50](#)

Technical data sheets

[FRS-R-50-FUSETRON DUAL ELEMENT FUSE CLASS RK5](#)

Technical service bulletins

[Datasheet - FNQ-30](#)