Elliott Electric Supply

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FS1512 12' Fiberglass Advent Stepladder Ia

Louisville Ladder

Catalog Number	FS1512
Manufacturer	Louisville Ladder
Description	Advent Fiberglass Stepladder, 300 LB Load Rating, 78 In Base Spread, 30-7/8 In Base Width, 137.127 In (Open Height);145.727 In (Closed Height) Overall Height, 3 In Rung Width, 3 In Step Depth, 11 Steps, 48 LB
Weight per unit	46.7 (lbs/each)
Product Category	Hand Tools - Ladders

Features

Load Capacity	94414

Descriptions

Description	12' FIBERGLASS ADVENT STEPLADDER IA
Special Features	Features: Protop - Versatile And Durable; Da Boot For Slip Resistant Footing; Inside Spreader Braces; Double-Rivet Step Construction; Wide Back Braces; A Multifunctional Top Designed To Increase Productivity; Hardware TRAY: Recessed Tray Provides Area To Secure Hardware From Falling Off The Top; Paint Bucket Holder: Convenient Recessed Tray Holds Quarter/Half/Full Gallon Paint Buckets; Drill Slots: Two Separate Drill Slots Make For A Variety Of Convenient Options Especially When Also Using The Paint Bucket

Manufacturer Information

Brand	Louisville
GTIN	00728865057198
UPC	728865057198

Taxonomies, Classifications, and Categories

Category Description	LADDERS
Type	Type IA

Packaging

Carton	1
Weight Per each	46.738

Uses, Certifications, and Standards

standard	CSA, ANSI A14.5, OSHA