



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2025 North Masch Branch Road Suite 105
76207-0000, TX Denton
Phone: 940-381-9070
Fax: 940-380-0325



FS250NJ 250 Va Enc CTRL XFRMR 277V-120V

Hammond Power Solutions

Catalog Number	FS250NJ
Manufacturer	Hammond Power Solutions
Description	General Purpose Enclosed Control Transformer, 277 PV, 120 SV, 250 Va
Weight per unit	7.6 (lbs/each)
Product Category	20191119163629

Features

Wattage	250
---------	-----

Dimensions and Weight

Height	4.3
Length	3.9
Width	6.6

Descriptions

Description	250 VA ENC CTRL XFRMR 277V-120V
extra long description	HMND FS250NJ FUSION 250VA 277-120
Long Description	General Purpose Enclosed Control Transformer, 277 PV, 120 SV, 250 VA
Product Type	Fusion 250VA 277-120
Special Features	An indoor enclosed control transformer for easy surface mounting.

Manufacturer Information

Brand	HPS Fusion™
GTIN	00803423107925
Manufacturers Part Number	FS250NJ
UPC	803423107925

Taxonomies, Classifications, and Categories

Category Description	CONTROL TRANSFORMERS
Type	Tranformer > Dry Type > Control > Ecnlosed

Packaging

Carton	1
Weight Per each	7.6



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2025 North Masch Branch Road Suite 105
76207-0000, TX Denton
Phone: 940-381-9070
Fax: 940-380-0325

Uses, Certifications, and Standards

Application	HVAC applications, signal ad alarm systems and motor control circuits.
Enclosure	FS-N1 - Indoor
Frequency Rating	50/60
Mounting	PANEL
standard	CSA, UL, CE
Temperature Rating	Typical 30 Average/ 40 Maximum