



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive
30336-0000, GA Atlanta
Phone: 470-237-5352
Fax: 470-237-5353



FSD8112C 12AWG 5/8" SNGL Wire Insldt Ferrule *Panduit Corporation*

Catalog Number	FSD8112C
Manufacturer	Panduit Corporation
Description	Covered Ferrules Single Wire Gray Din End Sleeve, 12 Awg, 12MM Pin Length.
Weight per unit	0.0011 (lbs/each)
Product Category	Small Terminals & Connectors

Features

insulation	Polypropylene
Material	Copper
media	Yes
Wire Size	12

Material, Color, and Finish

Color	Gray
Finish	Tinned

Descriptions

Description	12AWG 5/8" SNGL WIRE INSLTD FERRULE
extra long description	PAN FSD81-12-C Pan-Term® FSD81-12-C
Long Description	Covered ferrules single wire gray DIN end sleeve, 12 AWG, 12mm pin length.
Product Type	Pan-Term® FSD81-12-C Covered Single Wire Ferrules

Manufacturer Information

Brand	Panduit®
GTIN	00074983767458
Manufacturers Part Number	FSD81-12-C
UPC	074983767458

Taxonomies, Classifications, and Categories

Type	Covered Single Wire Ferrule
------	-----------------------------

Availability

minimum qty	100
-------------	-----

Packaging

Carton	100
Package	1000
Weight Per each	0.0011



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

4075 Boulder Ridge Drive
30336-0000, GA Atlanta
Phone: 470-237-5352
Fax: 470-237-5353

Uses, Certifications, and Standards

Mounting	5/8
standard	DIN 46228, CSA C22.2 No. 291-14, UL 486F, cULus 486F
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)