

Product Specifications



1/4" Flip Toggle Anchor Kit w/ Pan Head Combo Drive Screws

Part Number FTG14

Category Number 4740

UPC 781002854517

The Flip Toggle Anchor is a single piece, nylon body anchor with a metal tilting head ideal for use in drywall, plaster and hollow wall concrete blocks. Its unique tilting mechanism ensures a trouble-free installation that yields twice the strength of a regular toggle bolt of the same bolt diameter.



Physical Characteristics

Bit	IB2PC
Anchor Type	Flip Toggle
Drive Type	Phillips/Slotted
Head Type	Pan
Screw Size	1/4"-20 x 2-1/2"
Anchor Diameter	1/4"
Thread Pitch\Thread Per Inch	1/4"-20
Number of Pieces	10

Packaging Details

Kit Contains	(10) Flip Toggle Anchors, (10) 1/4"-20 x 2-1/2" Pan Phillips/Slotted Machine Screw
Standard Qty	1
Master Qty	10
Price Per	1
Package Length	9.60
Package Width	3.50
Package Height	1.50
Net Weight	0.68
Package Weight	.68

Performance Data

Tension Strength	1/2" Drywall: 148lbs, 5/8" Drywall: 240lbs, Hollow Concrete Block: 1070lbs
Safe Tension Load	1/2" Drywall: 74lbs, 5/8" Drywall: 120lbs, Hollow Concrete Block: 535lb
Shear Strength	1/2" Drywall: 274lbs, 5/8" Drywall: 418lbs, Hollow Concrete Block: 870lbs
Safe Shear Load	1/2" Drywall: 137lbs, 5/8" Drywall: 209lbs, Hollow Concrete Block: 600lb
Grip Range	1/2" to 2-1/8"
Hole Diameter	1/2"
Applications	Drywall, Hollow Block, Walls, and Ceilings
Special Features	Twice as Strong as Toggle Bolt, Fast and Easy Installation, Suitable for Overhead Applications, One Strap Design, Only Requires 1/2" Hole, Used with Any Bolt Length up to 3-3/4"

Certifications

RoHS Compliant	Yes
----------------	-----