

# Product Specifications



## 3/16" Flip Toggle Anchor Kit w/ Pan Head Combo Drive Screws

Part Number FTG316  
Category Number 4740  
UPC 781002854524

The Flip Toggle Anchor is a single piece, nylon body anchor with a metal tilting head ideal for use in drywall, plaster and hollow wall concrete blocks. Its unique tilting mechanism ensures a trouble-free installation that yields twice the strength of a regular toggle bolt of the same bolt diameter.



### Physical Characteristics

Bit	IB2PC
Anchor Type	Flip Toggle
Drive Type	Phillips/Slotted
Head Type	Pan
Screw Size	#10-24 x 2-1/2"
Anchor Diameter	3/16"
Thread Pitch\Thread Per Inch	#10-24
Number of Pieces	10

### Packaging Details

Kit Contains	(10) Flip Toggle Anchors, (10) #10-24 x 2-1/2" Pan Phillips/Slotted Machine Screw
Standard Qty	1
Master Qty	10
Price Per	1
Package Length	9.60
Package Width	3.50
Package Height	1.50
Net Weight	0.68
Package Weight	.68

### Performance Data

Tension Strength	1/2" Drywall: 134lbs, 5/8" Drywall: 214lbs, Hollow Concrete Block: 830lbs
Safe Tension Load	1/2" Drywall: 67lbs, 5/8" Drywall: 107lbs, Hollow Concrete Block: 415lb
Shear Strength	1/2" Drywall: 212lbs, 5/8" Drywall: 376lbs, Hollow Concrete Block: 870lbs
Grip Range	1/2" to 2-1/8"
Hole Diameter	1/2"
Applications	Drywall, Hollow Block, Walls, and Ceilings
Special Features	Twice as Strong as Toggle Bolt, Fast and Easy Installation, Suitable for Overhead Applications, One Strap Design, Only Requires 1/2" Hole, Used with Any Bolt Length up to 3-3/4"

### Certifications

RoHS Compliant	Yes
----------------	-----