COOPER LIGHTING SOLUTIONS - ALL-PRO™

DESCRIPTION

The ALL-PRO[™] LED Outdoor Security series is designed to provide superior security with the sustainability of LED Technology. Designed to be a direct replacement for traditional halogen and incandescent fixtures, these round low profile LED floodlights pack high performance into a small package. These fixtures are available in Flood, Motion and Dusk to Dawn configurations, and are made with durable die-cast aluminum.

Catalog #	Туре
Project	
Comments	Date

SPECIFICATION FEATURES

Construction

- Durable die-cast aluminum housing suitable for wet locations
- Powder coated bronze or white finish
- High reflectance
 polycarbonate reflector for
 maximum LED light output
- Tool-less head and motion sensor adjustment
- Tempered glass lens
- Suitable for wall or eave mounting using recessed junction box

Electrical

- 120VAC, 60Hz
- Maintenance-free LEDs with 50,000 hours of life
- Fixture operating temperature range from -30°C to 40°C
- UL and CUL listed for wet locations
- External supply wiring 75°C minimum
- Motion Configuration
- Motion sensor detects
- motion 180°up to 70 feet
 Adjustable motion timer from 1 to 12 minutes

- Integral photocell prevents lights from turning on with motion during daylight hours
- Manual override allows fixture to operate as a standard floodlight at night for 6 hours


Optics

- Precision optics for maximum efficiency
- 5000K color temperature
- 1600 Lumens
- Warranty
- 5 year limited warranty





LED TWIN ROUND SERIES

DIMENSIONS










6.6

[168mm]

Side View






Side View

Eave Mount

Front View



Wall Mount

ORDERING INFORMATION

Front View

Catalog Number	Product Description
MST18R17L	Bronze Twin LED with 180° Motion Sensor
MST18R17LW	White Twin LED with 180° Motion Sensor
FTR1740L	Bronze Twin LED Floodlight
FTR1740LW	White Twin LED Floodlight
FTR1740LPC	Bronze Twin LED Floodlight with integrated photo control
FTR1740LPCW	White Twin LED Floodlight with integrated photo control



Cooper Lighting Solutions 1121 Highway 74 South Peachtree City, GA 30269 P: 770.486.4800 www.cooperlighting.com

Specifications and dimensions subject to change without notice.

Innovation you can rely on™

SustainabL & Design

CERTIFICATION DATA UL/CUL Wet Location Listed Lighting Facts® Approved

TECHNICAL DATA

120V only -30°C to 40°C Temperature Rating External Supply Wiring 75° Minimum Wall and Eave Mount