



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



FV0511VQ1 WSPR CLNG Fan 50, 80, 110 CFM

Panasonic Corp Of N.A.

Catalog Number	FV0511VQ1
Manufacturer	Panasonic Corp Of N.A.
Description	Ventilation Fan, 1-Speed, Ceiling Mount Type; 10-1/4 Inch Length X 10-1/4 Inch Width X 7-3/8 Inch Height Size; UI (Canada and Us), Cul, Hvi Approval; 120 Volt Ac 60 Hertz Voltage Rating; 0.27 Amp Current Rating
Weight per unit	11.0 (lbs/each)
Product Category	Exhaust Fans

Features

Air Flow Rate	50/80/110 CFM
Current Rating	0.27 Amp
Duct Shape	Round
Duct Size	4 or 6 Inch Diameter
Grill Shape	Square
Grill Size	13 Inch Length x 13 Inch Width
Housing Shape	Square
Sound Level	0.4/0.6/0.9 Sones
Voltage Rating	120 Volt AC 60 Hertz

Material, Color, and Finish

Grill Material	POLYPROPYLENE
Housing Material	26 Gauge Zinc-Aluminum-Magnesium

Dimensions and Weight

Size	10-1/4 Inch Length x 10-1/4 Inch Width x 7-3/8 Inch Height
------	--



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Additional Information	Motor Type DC; Motor Bearing Type Ball; Power Rating 4/5.9/10.6 Watt; Speed Rating 756/821/957 RPM; Energy Efficiency 12.5/13.6/10.6 CFM per Watt; Static Pressure 0.1 Inch WG; Application Bathroom, Laundry Room, Sun Room, Basement or Garage; Applicable St
Commodity Description	Exhaust Fans
Description	WSPR CLNG FAN 50,80,110 CFM
extra long description	CEILING, 1-SPEED TYPE; 10-1/4 INCH LENGTH X 10-1/4 INCH WIDTH X 7-3/8 INCH HEIGHT SIZE; UL (CANADA AND US), CUL, HVI APPROVAL; 120 VOLT AC 60 HERTZ VOLTAGE RATING; 0.27 AMP CURRENT RATING; 26 GAUGE ZINC-ALUMINUM-MAGNESIUM COATED HOUSING MATERIAL; 50/80/110 CFM AIR FLOW RATE; 4 INCH OR 6 INCH DIAMETER DUCT SIZE; LESS THAN 0.3 SONES AT 0.1 INCH WG, 0.9 SONES AT 0.25 INCH WG SOUND LEVEL; 13 INCH LENGTH X 13 INCH WIDTH GRILL SIZE; POLY PRO GRILL MATERIAL; SQUARE HOUSING SHAPE; ROUND DUCT SHAPE; SQUARE GRILL SH
Long Description	VENTILATION FAN, 1-SPEED, CEILING MOUNT TYPE; 10-1/4 INCH LENGTH X 10-1/4 INCH WIDTH X 7-3/8 INCH HEIGHT SIZE; UL (CANADA AND US), CUL, HVI APPROVAL; 120 VOLT AC 60 HERTZ VOLTAGE RATING; 0.27 AMP CURRENT RATING
Product Type	Ventilation Fan

Manufacturer Information

Brand	Panasonic Corp Of N.A.
GTIN	00885170324930
Manufacturers Part Number	FV0511VQ1
UPC	885170324930

Taxonomies, Classifications, and Categories

Category Description	FANS & HEATERS
Type	1-Speed, Ceiling Mount

Packaging

Carton	1
Weight Per each	11

Uses, Certifications, and Standards

Approval	UL (Canada and US), CUL, HVI
----------	------------------------------