

Eaton FWH-1600A

Catalog Number: FWH-1600A

Eaton Bussmann series FWH high speed fuse, 1000 Vac, 800 Vdc, 1600A, 200 kAIC at 1000 Vac, 50 kAIC at 500 Vdc, None, High speed fuse, Blade end X blade end, Stud

General specifications



Product Name	Catalog Number
Eaton Bussmann series high speed cylindrical fuse	FWH-1600A
	UPC
	051712795906
EAN	Product Length/Depth
5027590020862	261 mm
Product Height	Product Width
107 mm	107 mm
Product Weight	Warranty
5509 g	Not Applicable
Compliances	Certifications
CE Marked	CSA Certified
RoHS Compliant	UL Recognized

Electrical data

Amperage Rating

1600 A

Voltage rating

500 Vac

Voltage type

AC

Interrupt rating

200 kAIC at 1000 Vac

50 kAIC at 500 Vdc

Class

Class aR

Pre arc (I2T)

290000

Clearing (I2T)

1400000

Watt losses

230 W

Product specification

Application

Semiconductor, DC Common bus, DC drives, Power converters/rectifiers

Fuse indicator

Non Indicating

Resources

Catalogs

[IEC high speed fuse links](#)

[Bussmann series complete full line catalog no. 1007](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)