

Eaton Bussmann series FWH high speed fuse

FWH-600A

UPC:051712150224

Dimensions:

- **Height:** 2.8 IN
- **Length:** 2.17 IN
- **Width:** 5.3 IN

Weight: .92 LB

Warranties:

- Not Applicable

Specifications:

- **Type:** High speed fuse
- **Application:** DC common bus, DC drives, power converters/rectifiers, reduced voltage starters
- **Voltage Rating:** 1000 Vdc
- **Amperage Rating:** 600A RMS
- **Interrupt Rating:** 200 kAIC at 1000 Vac, 50 kAIC at 500 Vdc
- **Connection:** Blade end X blade end
- **Mounting:** Stud
- **Packaging Type:** Standard
- **Clearing (I²T):** Clearing at 500V: 206000
- **Fuse Indicator:** Non Indicating
- **Pre Arc (I²T):** 41300
- **Watt Losses:** 108W

Supporting documents:

- [Product Catalog](#)
- [BUSS HIGH SPEED FUSE](#)
- [Product Datasheet](#)

Certifications:

- UL Recognized
- CSA Certified



Product compliance:

- CE Marked
- RoHS Compliant

© 2016 Eaton. All rights reserved.