

## Eaton Bussmann series FWX high speed fuse

### FWX-35A

UPC:051712150477

#### Dimensions:

- **Height:** .89 IN
- **Length:** 3.44 IN
- **Width:** .91 IN

**Weight:**.12 LB

#### Warranties:

- Not Applicable

#### Specifications:

- **Type:** High speed fuse
- **Application:** DC common bus, DC drives, power converters/rectifiers, reduced voltage starters
- **Voltage Rating:** 600V
- **Amperage Rating:** 35A RMS
- **Interrupt Rating:** 200 kAIC Vac, 50 kAIC at 250 Vdc
- **Connection:** Blade end X blade end
- **Mounting:** Stud
- **Packaging Type:** Standard
- **Clearing (I<sup>2</sup>T):** Clearing at 250V: 230
- **Fuse Indicator:** Non Indicating
- **Pre Arc (I<sup>2</sup>T):** 50
- **Watt Losses:** 4.2W

#### Supporting documents:

- [Product Catalog](#)
- [Product Datasheet](#)

#### Certifications:

- CSA Certified
- UL Recognized

#### Product compliance:



- RoHS Compliant
- CE Marked

---

© 2016 Eaton. All rights reserved.