


# FZH400PSQ

New clean design, compact, tough and good looking cast aluminum housing with 2" Integra Hood, steel trunnion mount for easy surface mounting and aiming flexibility. Factory wired for 277V. Lamp supplied.

Color: Bronze

Weight: 29.7 lbs




## Lamp Info

Type: ED28  
Watts: 400W  
Shape/Size: N/A  
Base: N/A  
ANSI: N/A  
Hours: 15,000  
Lamp Lumens: 40,000  
Efficacy: 89 LPW

## Ballast Info

Type: CWA-HPF QT  
120V: 3.5/4.0A  
208V: 2.0/2.3A  
240V: 1.8/2.0A  
277V: 1.5/1.8A  
Input Watts: 450W  
Efficiency: 89%



## Technical Specifications

### UL Listing:

Suitable for wet locations. Suitable for mounting within 1.2m (4ft) of the ground.

### Housing:

Precision die cast aluminum .

### Reflector:

High quality anodized aluminum .

### Lens:

Tempered shock resistant glass.

### Lens Gasket:

Molded one-piece silicone in die cast retaining groove to remain in place during relamping.

### Socket:

Glazed porcelain 4kv pulse rated with nickel plated screw shell and spring contacts.

### Finish:

Our environmentally friendly polyester powder coatings are formulated for high-durability and long-lasting color, and contains no VOC or toxic heavy metals.

### EPA:

1.3.

### Pulse Start:

Pulse Start metal halide for increased lamp life, lumen maintenance, color uniformity and efficiency.

### Patents:

Pat. D547,477.

### EISA 2007 Compliant:

This product complies with the new law for metal halide ballast efficiency. This law goes into effect January 1st, 2008. Pulse Start offers Longer Lamp Life, Faster Startup and Faster Restrike.