



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GAL190 1", 90D RGD Elb

Robroy/Ecn Korns

Catalog Number	GAL190
Manufacturer	Robroy/Ecn Korns
Description	Standard Radius Elbow, 1 In Trade Size, Hot Dip Galvanized, 90 ° Connection Orientation, 5.75 In Bend Radius, External Threaded Connection, 189 LB/100
Weight per unit	1.9 (lbs/each)
Product Category	Steel

Features

Applicable Standard	ANSI C80.1
Bend Angle	90 Degree
End Type	EXTERNAL THREADED
Material	Steel

Descriptions

Additional Information	Size 1.049 Inch ID x 1.315 Inch OD
Also Known As...	Sweep Elbow Pre-Fab
Commodity Description	ELBOWS-COUPPLINGS-NIPPLES - STEEL
Description	1",90D RGD ELB
extra long description	STANDARD RADIUS TYPE; STEEL MATERIAL; GALVANIZED FINISH; UL (CANADA AND US), UL 6, CSA C22.1/C22.2, NOM APPROVAL; ANSI/NFPA 70, NEC 344, ISO 9001 APPLICABLE STANDARD; 25 PER CARTON STANDARD PACKAGE; 1 INCH TRADE SIZE; EXTERNAL THREADED END TYPE; 90 DEGREE BEND ANGLE; 5.75 INCH BEND RADIUS; APPLICATION INDOOR/OUTDOOR; GALELB MODEL

Manufacturer Information

Brand	EC-KORNS
GTIN	00784011001637
Model	GALELB
UPC	784011001637

Taxonomies, Classifications, and Categories

Category Description	RIGID ELBOWS
Type	STANDARD RADIUS



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Package	25
Standard Package	25 PER CARTON
Weight Per each	1.89

Uses, Certifications, and Standards

Approval	UL 6, CSA C22.2, UL (Canada and US), ETL
----------	--