

Galvanized Elbows, Couplings

| Rigid Steel Conduit | | List Price per 100 | UPC | | | | Standard | Weight per 100 |
|---|-------------|-----------------------|--------|--------|-------|-------|----------|-------------------|
| 90 [°] –45° Hot Dip Galvanized Elbows* | Size | Pieces | 90° | 45° | 60° | 30º | Carton | Pieces (lbs) |
| | 1/2" | 339.01 | 00161 | 00181▲ | 00116 | 00146 | 50 | 75 |
| NOTE: Weights shown are approximate for 90° elbows. To arrive at weights for 60° elbows deduct 10%, for 45° elbows deduct 15% and 30° | 3⁄4" | 405.56 | 00162▲ | 00182▲ | 00117 | 00147 | 50 | 109 |
| | 1" | 605.61 | 00163▲ | 00183▲ | 00118 | 00148 | 25 | 189 |
| | <u>1¼"</u> | 866.54 | 00164 | 00184▲ | 00119 | 00149 | 10 | 303 |
| | 1½" | 1128.30 | 00165▲ | 00185▲ | 00120 | 00150 | 15 | 416 |
| | 2" | 1628.98 | 00166▲ | 00186▲ | 00121 | 00151 | 10 | 635 |
| elbows deduct 20%. | 2 ½" | 2977.22 | 00167▲ | 00187▲ | 00122 | 00152 | Bulk | 1217 |
| | 3" | 4331.96 | 00168▲ | 00188▲ | 00123 | 00153 | Bulk | 1801 |
| | 3½" | 6775.00 | 00169▲ | 00189▲ | 00124 | 00154 | Bulk | 2684 |
| | 4" | 7768.80 | 00170▲ | 00190▲ | 00125 | 00155 | Bulk | 3166 |
| | 5" | 18394.97 | 00172 | 00192▲ | 00126 | 00156 | Bulk | 6339 |
| | 6" | 27678.98 | 00174 | 00194 | 00127 | 00157 | Bulk | 10575 |

Rigid Steel Conduit Galvanized Couplings

| Size | List Price per 100 Pieces | UPC | Standard Carton | Weight per 100 Pieces (Ibs) |
|-------------|---------------------------------|--------|--------------------|-----------------------------------|
| 1⁄2" | 100.57 | 00131▲ | 100 | 12 |
| 3/4" | 123.45 | 00132▲ | 50 | 18 |
| 1" | 182.84 | 00133▲ | 50 | 31 |
| 1¼" | 228.60 | 00134▲ | 50 | 40 |
| 1½" | 288.70 | 00135▲ | 50 | 52 |
| 2" | 381.55 | 00136▲ | 20 | 73 |
| 2 ½" | 892.13 | 00137▲ | 12 | 179 |
| 3" | 1155.08 | 00138▲ | 12 | 221 |
| 3½" | 1548.89 | 00139▲ | 12 | 355 |
| 4" | 1555.51 | 00140▲ | 12 | 308 |
| 5" | 3589.58 | 00142▲ | Bulk | 482 |
| 6" | 4984.25 | 00144▲ | Bulk | 775 |

PREFIX: GALCPLG (SIZE)

| Radius Chart This chart shows the radius for each of our standard radius elbows, regardless of the degree of bend. We offer larger radius elbows as shown in this price sheet but standard is the smallest radius for each size. | Size 1/2" 3/4" 1" 1-1/4" 1-1/2" 2" 2-1/2" 3" 3-1/2" 4" 5" 6" | Radius 4.25" 4.50" 5.75" 7.25" 8.25" 9.50" 10.50" 13.00" 15.00" 16.00" 24.00" 30.00" | |
|---|--|--|--|
|---|--|--|--|

*UL Listed & Labeled

Availability Codes Stock = ▲ 5 Days = ■ 10 Days = ●



ELBOWS

Galvanized
EMT
IMC
Aluminum

COUPLINGS

GalvanizedAluminum

CLAMPS

The Original

"KORNS CLAMP"

- Right Angle (RA) Conduit Supports
- Edge Type (ET) Conduit Supports
- J-Clamps
- One Hole Straps
- Clampback Spacers
- U-Bolts
- □ SS Hardware
- Parallels (PAR)
- Beam Clamps

NIPPLES

Galvanized Aluminum

MANUFACTURERS UPC #784011

Price List Catalog F-162

Effective May 1, 2000 Supercedes all previous

Revised: 3-22-2001 Dimensional and Material Specifications where applicable: Underwriters' Laboratories No. 6 A.N.S.I. C80.1, Fed. Specs. WW-C-581e