



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## GB4C 4AWG Ground Conn *Burndy LLC*

Catalog Number	GB4C
Manufacturer	Burndy LLC
Description	Mechanical Grounding Connector, Cable to 1/4" Thick Bar, 8 Awg (Sol)- 4 Awg (STR), 3/8" STUD1-1/4 In Width.
Weight per unit	0.1540 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Material	COPPER ALLOY
----------	--------------

### Descriptions

Description	4AWG GROUND CONN
extra long description	BUR GB4C 8SOL-4STR CU BAR 1 PC SEP
Long Description	Mechanical Grounding Connector, Cable to 1/4" Thick Bar, 8 AWG (Sol)- 4 AWG (Str), 3/8" Stud1-1/4 IN Width.
Product Type	Mechanical
Special Features	Features: High Copper Alloy Ground Connector For Joining A Range Of Cable To 1/4 IN Thick Bar, Type GB Separates Cable From Bar, One-Wrench Installation, UL467 Listed, The High Copper Alloy Cast Body And DURIUM Bolts, Nuts, And Lockwashers Make The GB And GBM Suitable For Direct Burial In Concrete Or Ground, Width: 1-1/4 IN, Installation Torque: 240 IN-LB, Bar Thickness: 1/4 IN, Height: 1-1/2 IN

### Manufacturer Information

Brand	BURNDY
GTIN	00781810231180
Manufacturers Part Number	GB4C
sub brand	Mechanical Connector
UPC	781810231180

### Taxonomies, Classifications, and Categories

Category Description	SERVICE ENTRANCE FITTINGS: Weatherheads & Grounding Fittings & Ground Rods
Type	GB

### Packaging

Carton	1
Weight Per each	0.154

### Uses, Certifications, and Standards

Application	For Copper Cable To Bar, Direct Burial Cable
standard	UL467