



# GC2525CT, Mechanical Grounding Connector, 2 Cables to Bar

By Burndy  
Catalog # GC2525CT



Cast Copper Alloy Cable Tray Ground Clamp, #6 Sol. (.162 Dia.)  
-1/0 Str. (.372 Dia.), 1.12 in L, 1.45 in W, Tin Plated.

## Application

For Direct Burial Applications In Concrete Or Earth And For Used With Aluminum Or Galvanized Steel Cable Tray

## General

EU RoHS Indicator	Yes
Installation Torque	240 lb-in
Recommended in-lb	
Material	Copper Alloy
Plated	Y
Plating Type	Tin
Sub Brand	MECHANICAL CONNECTOR
Type	GC-CT
UPC	781810035504
UPC 12 Digit	7818100355044

## Dimensions

Dimension - B Length inch	1.12 in
Dimension - Cross Flats inch	0.56 in
Dimension - Height inch	1.95 in
Dimension - Width inch	1.45 in
Dimension - Width mm	37 mm

## Conductor Related

Conductor - AL Str Size	6 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG
Conductor - AL Str Size Range	6 AWG-1/0 AWG
Conductor - Copper Solid Size	6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG
Conductor - Copper Solid Size Range	6 AWG-1/0 AWG
Conductor - Copper Str Size	7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0
Conductor - Copper Str Size Range	7 AWG - 1/0 AWG

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	EX
UL Listed	Yes

## Logistics

Minimum Pack Quantity	1
-----------------------	---

## Product Assets

- [3D Models - GC2525CT\\_MODEL-IGES](#)
- [3D Models - GC2525CT\\_MODEL-STEP](#)
- [3D Models - GC2525CT\\_MODEL-PDF](#)
- [Catalogs - Full Line BURNDY Catalog](#)
- [Customer Notices - Prop 65 Notice](#)
- [Sales Drawings - sc082752-01](#)



A proud member of the Hubbell Family.

