



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449



GC38 3/8" Flex Conn D/C Screw In *Appleton/Oz Gedney*

Catalog Number	GC38
Manufacturer	Appleton/Oz Gedney
Description	Features:0.38IN Dia X 1.3IN Length, For Flexible Metal Conduit, Standard:UI 514B, Csa C22.2, Nema FB-1, Size:0.375IN, Material:Zinc Die Cast
Weight per unit	0.0500 (lbs/each)
Product Category	Liquid Tight Fittings

Features

angle	Straight
connection	Male NPS Thread
Connector Type	Screw In
insulation	Non Insulated
Material	Zinc Die Cast

Material, Color, and Finish

Color	Metallic
Finish	Natural

Dimensions and Weight

Size	0.375
------	-------

Descriptions

Description	3/8" FLEX CONN D/C SCREW IN
extra long description	EGS GC-38 3/8 IN SCREW IN CONN
Long Description	Features:0.38IN Dia X 1.3IN Length, For Flexible Metal Conduit, Standard:UL 514B, CSA C22.2, NEMA FB-1, Size:0.375IN, Material:Zinc Die Cast
Product Type	3/8 In Screw In Conn
Special Features	0.38 IN Dia X 1.3 IN Length, For Flexible Metal Conduit

Manufacturer Information

Brand	Appleton
GTIN	00687855203383
Manufacturers Part Number	GC38
UPC	687855203383

Taxonomies, Classifications, and Categories

Category Description	FLEX & MC FITTINGS
Type	Screw In Connector

Trade Size

Trade Size	0-50
------------	------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

5018 W Main Street
74701-0000, OK Durant
Phone: 580-745-5448
Fax: 580-745-5449

Packaging

Carton	50
Package	500
Weight Per each	0.05

Uses, Certifications, and Standards

Application	Screw-In Connector for flexible metal conduit
environmental conditions	Dry Location
nema rating	FB-1
standard	UL Standard: 514B; UL Listed: E32539, CSA Standard: C22.2 No. 18.3, CSA Certified: 208044; NEMA: FB-1