

Specifications



Eaton GDB-10A

Eaton GDB Series Fast-acting fuse, 10A, 250 Vac or less, 32 Vdc (self certified)

General specifications

PRODUCT NAME	Eaton Bussmann series GDB fast-acting fuse
CATALOG NUMBER	GDB-10A
UPC	051712431866
PRODUCT HEIGHT	20 mm
PRODUCT DIAMETER	5.2 mm
PRODUCT WEIGHT	0.7 g
WARRANTY	Not Applicable
COMPLIANCES	CE Marked RoHS Compliant CCC Marked
CERTIFICATIONS	VDE
GLOBAL CATALOG	GDB-10A

Product specifications

AMPERAGE RATING	10 A
FREQUENCY RATING - MAX	50 Hz
FREQUENCY RATING - MIN	50 Hz
VOLTAGE DROP	120 mV maximum
INTERRUPT RATING	35 AIC at 250 Vac
FUSE INDICATOR	Non-indicating
CONNECTION	Ferrule end x ferrule end
MATERIAL	Glass tube Nickel-plated brass end cap construction
QUANTITY	5
VOLTAGE RATING	250 Vac or less, 32 Vdc (self certified)
TYPE	Electronic
APPLICATION	Electronic circuits

Resources

SPECIFICATIONS AND DATASHEETS

[Eaton Specification Sheet - GDB-10A](#)

[Eaton GDB fast-acting glass tube fuses data sheet](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

