



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GDB500MA 500MA 250V Fa Low-Break IEC Glass Fuse *Bussmann Fuses*

Catalog Number	GDB500MA
Manufacturer	Bussmann Fuses
Description	Fuse, Fast Acting Fuse Speed, Ferrule End X Ferrule End Connection, 500 Ma, 250 V Ac, Glass (Tube);Brass (End Cap) Material, Ferrule Terminal, 5.2 MM Diameter, 20 MM Overall Length, 0.01 LB
Weight per unit	0.0100 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	0.500A
connection	Ferrule End X Ferrule End
dimensions	X X 0.7874 IN

Dimensions and Weight

Size	5.20 mm Diameter X 20.00 mm Height
------	------------------------------------

Descriptions

Description	500MA 250V FA LOW-BREAK IEC GLASS FUSE
extra long description	BUSS GDB-500MA BUSS SMALL DIMENSION
Features	Fast-acting, low breaking capacity 5 mm x 20 mm ferrule fuse designed to IEC 60127-2 for overcurrent protection of electronic circuits. Install into a Bussmann Series fuse holder, block, or fuse clip, or purchase with available axial leads for thru-hole installation Eaton's GDB fast-acting, low breaking capacity 5mm x 20mm ferrule fuses are designed to IEC 60127-2 for overcurrent protection of electronic circuits. Order in cartridge fuse format and install into a Bussmann Series fuse holder, block, or fuse
Special Features	Low Breaking Capacity, Interrupt Rating 35 Amp at 250 V, Material Glass Tube, Nickel Plated Brass Endcap

Manufacturer Information

Brand	Eaton
GTIN	00051712431736
UPC	051712431736

Taxonomies, Classifications, and Categories

Category Description	GLASS FUSES (and ceramic)
Type	Fast-Acting Fuse

Packaging

Carton	5
Weight Per each	0.01



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Frequency Rating	50
standard	VDE,CE Marked,CCC Marked,RoHS Compliant