



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

3168 SW Loop 436  
75633-0000, TX Carthage  
Phone: 903-694-9924  
Fax: 903-694-9928



## GE232MVN 1-2 F32T8 Inst Start Ballast 120-277V Norm Bal Fac

*Ge By Current Lamps*

Catalog Number	GE232MVN
Manufacturer	Ge By Current Lamps
Description	Ge Ultramax™, 60 HZ, Normal Ballast Factor, Instant Start, 9.5 In Length, 1.3 In Width, 1.18 In Height, 2 or 1-F32T8
Weight per unit	1.2 (lbs/each)
Product Category	Electronic Linear Fluorescent

### Features

Ballast Factor	Normal
start type	Instant Start

### Dimensions and Weight

Height	1.18
Length	9.5
Width	1.3

### Descriptions

Description	1-2 F32T8 INST START BALLAST 120-277V NORM BAL FAC
extra long description	GEL GE232MAX-G-N 72275 ELECTRONIC B
Long Description	GE UltraMax™, 60 Hz, Normal Ballast Factor, Instant Start, 9.5 IN Length, 1.3 IN Width, 1.18 IN Height, 2 or 1-F32T8
Product Type	72275 Electronic Ballast
Special Features	GE232MAX-G-N (Replaces GE-232-MV-N) Designation

### Manufacturer Information

Brand	GE Current, a Daintree company
GTIN	00043168722759
Manufacturers Part Number	GE232MAX-G-N
UPC	043168722759

### Taxonomies, Classifications, and Categories

Category Description	ELECTRONIC BALLAST
Type	Ballasts_Fluorescent_Electronic

### Availability

Status	Inactive
--------	----------

### Packaging

Carton	1
Package	10
Weight Per each	1.17

### Uses, Certifications, and Standards

Frequency Rating	60
------------------	----