

Specifications



Photo is representative



Eaton GFEP120

Eaton BR GFCI circuit breaker, Industrial ground fault thermal-magnetic equipment protector, 20 A, 10 kAIC, Single-pole, 120 V, GFEP, Common, #14-4 AWG, Ground fault circuit interrupter, GFI

General specifications

PRODUCT NAME	Eaton BR GFCI circuit breaker
CATALOG NUMBER	GFEP120
UPC	786676382052
PRODUCT LENGTH/DEPTH	3 in
PRODUCT HEIGHT	1.25 in
PRODUCT WIDTH	4.75 in
PRODUCT WEIGHT	0.45 lb
WARRANTY	Limited lifetime
CERTIFICATIONS	UL 489
CATALOG NOTES	Meets Federal Spec Classification W-C375

Product specifications

AMPERAGE RATING	20 A
VOLTAGE RATING	120 V
TRIP TYPE	Common
CIRCUIT PROTECTION	Ground fault circuit interrupter
INDICATORS	GFI
INTERRUPT RATING	10 kAIC
MAIN CIRCUIT BREAKER	GFEP
WIRE SIZE	#14-4 AWG
NUMBER OF POLES	Single-pole
TYPE	Industrial ground fault thermal-magnetic equipment protector

Resources

CATALOGS	Residential and Light Commercial, Loadcenters and Circuit Breakers, Volume 1 Tab 1
SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - GFEP120
WARRANTY GUIDES	Eaton type BR circuit breaker limited warranty June 2024

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc

Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

