# Eaton GFTCB215

## Catalog Number: GFTCB215

Eaton BR GFCI circuit breaker, Ground fault personnel protection circuit breakers, 15 A, 10 kAIC, Two-pole, 120/240 V, GFTCB, Common, #14-4 AWG, Ground fault circuit interrupter, GFI

#### General specifications



Eaton BR GFCI circuit breaker

UPC

786676025607

**Product Height** 

2 in

**Product Weight** 

0.7 lb

Certifications

UL 943

UL 489

Catalog Number

GFTCB215

Product Length/Depth

4.5 in

Product Width

2.75 in

Warranty

10 year

Catalog Notes

Meets Federal Spec Classification W-

C375



Photo is representative



### default Taxonomy Attribute Label

Type

Ground fault personnel protection circuit breakers

**Amperage Rating** 

15 A

Voltage rating

120/240 V

Trip Type

Common

Circuit protection

Ground fault circuit interrupter

Indicators

GFI

Interrupt rating

10 kAIC

Main circuit breaker

**GFTCB** 

Wire size

#14-4 AWG

Number of poles

Two-pole

#### Resources

**Brochures** 

Loadcenters and Circuit Breakers

Specifications and datasheets

Eaton Specification Sheet - GFTCB215



Eaton Corporation plc Eaton House 30 Pembroke Road Dublin 4, Ireland Eaton.com

Reserved.

Eaton is a registered trademark.

All other trademarks are © 2024 Eaton. All Rights property of their respective owners.



Eaton.com/socialmedia