

Eaton GFTCB225

Catalog Number: GFTCB225

Eaton BR GFCI circuit breaker, Ground fault personnel protection circuit breakers, 25 A, 10 kAIC, Two-pole, 120/240 V, GFTCB, Common, #14-4 AWG, Ground fault circuit interrupter, GFI

General specifications



Photo is representative

| | |
|-------------------------------|--|
| Product Name | Catalog Number |
| Eaton BR GFCI circuit breaker | GFTCB225 |
| UPC | Product Length/Depth |
| 786676025966 | 4.5 in |
| Product Height | Product Width |
| 2 in | 2.75 in |
| Product Weight | Warranty |
| 0.7 lb | 10 year |
| Certifications | Catalog Notes |
| UL 943 UL 489 | Meets Federal Spec Classification W-C375 |

Type

Ground fault personnel protection circuit breakers

Amperage Rating

25 A

Voltage rating

120/240 V

Trip Type

Common

Circuit protection

Ground fault circuit interrupter

Indicators

GFI

Interrupt rating

10 kAIC

Main circuit breaker

GFTCB

Wire size

#14-4 AWG

Number of poles

Two-pole

Brochures

[Loadcenters and Circuit Breakers](#)

[Specifications and datasheets](#)

[Eaton Specification Sheet - GFTCB225](#)