

Eaton GFTCB250

Catalog Number: GFTCB250

Eaton BR GFCI circuit breaker, Ground fault personnel protection circuit breakers, 50 A, 10 kAIC, Two-pole, 120/240 V, GFTCB, Common, #14-4 AWG, Ground fault circuit interrupter, GFI

General specifications



Product Name	Catalog Number
Eaton BR GFCI circuit breaker	GFTCB250
UPC	Product Length/Depth
786676025997	4.5 in
Product Height	Product Width
2 in	2.75 in
Product Weight	Warranty
0.7 lb	10 year
Certifications	Catalog Notes
UL 943 UL 489	Meets Federal Spec Classification W-C375

Type

Ground fault personnel protection circuit breakers

Amperage Rating

50 A

Voltage rating

120/240 V

Trip Type

Common

Circuit protection

Ground fault circuit interrupter

Indicators

GFI

Interrupt rating

10 kAIC

Main circuit breaker

GFTCB

Wire size

#14-4 AWG

Number of poles

Two-pole

Brochures

[Loadcenters and Circuit Breakers](#)

Specifications and datasheets

[Eaton Specification Sheet - GFTCB250](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)