



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9707 Broadway St Suite 100  
78217-0000, TX San Antonio  
Phone: 210-646-6950  
Fax: 210-646-6192



## GHB2040 Type GHB BRKR 2P 40A 277/480VAC Max 125/250VDC Max *Eaton Corp*

Catalog Number	GHB2040
Manufacturer	Eaton Corp
Description	Eaton Series C Complete Molded Case Circuit Breaker, G-Frame, GHB, Complete Breaker, Fixed Thermal, Fixed Magnetic Trip Type, Two-Pole, 40 A, 480Y/277 Vac, 125/250 VDC, 50/60 HZ
Weight per unit	1.2 (lbs/each)
Product Category	2 Pole

### Features

Current Rating	40 A
dimensions	2.6300 IN X 2.0000 IN X 4.0000 IN
frame	G
Poles	Two-pole
Voltage Rating	480Y/277 Vac, 125/250 Vdc

### Descriptions

Description	TYPE GHB BRKR 2P 40A 277/480VAC MAX 125/250VDC MAX
extra long description	ETN GHB2040 GHB CB 2P 40A 277/480VA
Features	Experience the superior quality of the Eaton Series C Molded Case Circuit Breaker. The Series C circuit breaker is ideal for panelboards, switchboards, motor control centers, and busway applications. Choose from a premier selection of trip units including thermal magnetic, electronic, and magnetic only switches. Available for systems up to 600 VAC or 250 VDC with current ratings up to 800A.
Long Description	Eaton Series C complete molded case circuit breaker, G-frame, GHB, Complete breaker, Fixed thermal, Fixed magnetic trip type, Two-pole, 40 A, 480Y/277 Vac, 125/250 Vdc, 50/60 Hz
Product Type	GHB CB 2P 40A 277/480VAC Max 125/250VDC

### Manufacturer Information

Brand	Eaton
GTIN	00786679911228
Manufacturers Part Number	GHB2040
UPC	786679911228

### Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Molded case circuit breaker

### Availability

Status	Inactive
--------	----------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

9707 Broadway St Suite 100  
78217-0000, TX San Antonio  
Phone: 210-646-6950  
Fax: 210-646-6192

## Packaging

Carton ..... 1

Weight Per each ..... 1.15

## Uses, Certifications, and Standards

Application ..... Elec Assemblies, Panels & OEM - Electrical Assemblies and  
EOEMs - Other

standard ..... UL Listed,Federal Specifications Classification W-C375B