

Eaton GHB3035

Catalog Number: GHB3035

Eaton Series C complete molded case circuit breaker, G-frame, GHB, Complete breaker, Fixed thermal, Fixed magnetic trip type, Three-pole, 35 A, 480Y/277 Vac, 125/250 Vdc, 50/60 Hz



Photo is representative

General specifications

Product Name

Eaton Series C complete molded case circuit breaker

Catalog Number

GHB3035

UPC

786679172605

Product Length/Depth

2.63 in

Product Height

4 in

Product Width

3 in

Product Weight

1.75 lb

Warranty

Eaton Selling Policy 25-000, one (1) year Federal Specifications Classification W- from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

C375B

Certifications

UL Listed

defaultTaxonomyAttributeLabel

Type

Molded case circuit breaker

Amperage Rating

35 A

Voltage rating

480Y/277 Vac, 125/250 Vdc

Trip Type

Fixed thermal, fixed magnetic

Circuit breaker type

GHB

Circuit breaker frame type

Complete breaker

Series

Series C

Frame

G

Frequency rating

50/60 Hz

Interrupt rating

14 kAIC at 480Y/277 Vac

65 kAIC at 240 Vac

Number of poles

Three-pole

Resources

Application notes

[Application of Tap Rules to Molded Case Breaker Terminals](#)

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

Brochures

[Motor protection circuit breakers product aid](#)

[Circuit breaker motor operators product aid](#)

[Multi-wire lugs product aid](#)

[MOEM MCCB Product Selection Guide](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[StrandAble terminals product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[Breaker service centers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

[Molded case circuit breakers catalog](#)

Drawings

[G-frame Molded Case Circuit Breaker Drawing](#)

Installation instructions

[Series C GB/GHB/GDB Circuit Breakers - IL](#)

Multimedia

[Circuit breakers explained](#)

[Circuit Breakers Explained](#)

Specifications and datasheets

[Series C G-Frame Time Current Curves](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[Eaton Specification Sheet - GHB3035](#)

[MOEM MCCB product selection guide](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[Series C F-Frame molded case circuit breakers](#)

Time/current curves

[Type GHB/GHC/GD/GPS 2 and 3-pole, 15-100A Time Curve](#)

Warranty guides

[Selling Policy 25-000 - Distribution and Control Products and Services](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)