



Powering Business Worldwide

pe.eaton.com

Eaton Series C complete molded case circuit breaker

GHB3040

UPC:786679911280

Dimensions:

- **Height:** 3.8 IN
- **Length:** 6.5 IN
- **Width:** 3.8 IN

Weight:1.75 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Molded case circuit breaker
- **Amperage Rating:** 40A
- **Interrupt Rating:** 65 kAIC at 240 Vac, 14 kAIC at 480Y/277 Vac
- **Number Of Poles:** Three-pole
- **Voltage Rating:** 480Y/277 Vac, 125/250 Vdc
- **Trip Type:** Fixed thermal, fixed magnetic
- **Circuit Breaker Type:** GHB
- **Circuit Breaker Frame Type:** Complete breaker
- **Frequency Rating:** 50/60 Hz
- **Frame Size:** G-frame
- **Series:** Series C

Supporting documents:

- [MOEM MCCB Product Selection Guide](#)
- [Eatons Volume 4-Circuit Protection](#)
- [G-frame Molded Case Circuit Breaker Drawing](#)
- [Series C GB/GHB/GDB Circuit Breakers - IL](#)
- [Series C G-Frame Time Current Curves](#)



- Type GHB/GHC/GD/GPS 2 and 3-pole, 15-100A Time Curve

Certifications:

- UL Listed

Product compliance:

- Federal Specifications Classification W-C375B

© 2016 Eaton. All rights reserved.