

Eaton GHC1015

Catalog Number: GHC1015

Eaton Series C complete molded case circuit breaker, G-frame, GHC, Complete breaker, Fixed thermal, fixed magnetic trip type, Single-pole, 15A, 277 Vac, 125 Vdc, 14 kAIC at 277 Vac, 50/60 Hz



Photo is representative

General specifications

Product Name	Catalog Number
Eaton Series C complete molded case circuit breaker	GHC1015
	UPC
	786679173954
Product Length/Depth	Product Height
2.63 in	4.88 in
Product Width	Product Weight
1 in	0.75 lb
Warranty	Certifications
Eaton Selling Policy 25-000, one (1) year UL Listed from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.	

defaultTaxonomyAttributeLabel

Amperage Rating

15 A

Voltage rating

277 Vac, 125 Vdc

Trip Type

Fixed thermal, fixed magnetic

Circuit breaker type

GHC

Circuit breaker frame type

Complete breaker

Series

Series C

Frame

G

Frequency rating

50/60 Hz

Interrupt rating

14 kAIC at 277 Vac

Number of poles

Single-pole

Resources

Application notes

[Application of Multi-Wire Terminals for Molded Case Circuit Breakers](#)

[UL listed 100%-rated molded case circuit breakers](#)

[Application of Tap Rules to Molded Case Breaker Terminals](#)

Brochures

[Circuit breaker motor operators product aid](#)

[Power metering and monitoring with Modbus RTU product aid](#)

[MOEM MCCB Product Selection Guide](#)

[Plug-in adapters for molded case circuit breakers product aid](#)

[Current limiting Series C molded case circuit breakers product aid](#)

[Multi-wire lugs product aid](#)

[StrandAble terminals product aid](#)

[Motor protection circuit breakers product aid](#)

[Breaker service centers](#)

Catalogs

[Molded case circuit breakers catalog](#)

[Eaton's Volume 4—Circuit Protection](#)

Drawings

[G-frame Molded Case Circuit Breaker Drawing](#)

Installation instructions

[Series C GB/GHB/GDB Circuit Breakers - IL](#)

[Series C GC/GHC Circuit Breaker - IL](#)

Multimedia

[Circuit Breakers Explained](#)

[Circuit breakers explained](#)

Specifications and datasheets

[Series C F-Frame molded case circuit breakers](#)

[Series C J-Frame molded case circuit breakers time current curves](#)

[Series C G-Frame molded case circuit breakers time current curves](#)

[MOEM MCCB product selection guide](#)

[Eaton Specification Sheet - GHC1015](#)

[Series C G-Frame Time Current Curves](#)

Time/current curves

[Type GHB/GHC/GD/GPS 2 and 3-pole, 15-100A Time Curve](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)