ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

GHG2622301L0003 20A, 690V 3P Exp DSCNCT SW

Crouse-Hinds

Catalog Number	GHG2622301L0003
Manufacturer	Crouse-Hinds
Description	Exp Protected Disconnect Switches
Weight per unit	3.3 (lbs/each)
Product Category	Distribution Equipment

Features

amperage rating	20
Contact Configuration	1 NO
Poles	3
Voltage Rating	240/600 Vac

Dimensions and Weight

Depth	4.33
Height	6.69
Width	5.08

Descriptions

Description	20A,690V 3P EXP DSCNCT SW
extra long description	CRS-H GHG2622301L0003 EXP PROTECTED
Long Description	EXP PROTECTED DISCONNECT SWITCHES
Product Type	Exp Protected Disconnect Switches
Special Features	Non-Metallic Enclosure, Power Rating 14.3 Hp at 240 Vac, 12.2 Hp at 600 Vac

Manufacturer Information

Brand	CEAG (EXCEPT I.S. PRODUCT)
GTIN	00622692050899
Manufacturers Part Number	GHG2622301L0003
UPC	622692050899

Taxonomies, Classifications, and Categories

Category Description	DISCONNECTS

Packaging

Carton	1
Weight Per each	3.2999

Uses, Certifications, and Standards

Application	Metallic Conduit or Cable System For Surface Mounting To Control Motor, Lighting and Other Circuits
Enclosure	Class I Div 2 Group A B C D, Class I Zones 1 2, Class II Div 1 Group E F G, Class II Div 2 Group F G, NEMA 4X, IP66
standard	UL 94, CSA C22.2