

Eaton GHQ1015

Catalog Number: GHQ1015

Type GHQ Circuit Breakers, 15A, 14 kAIC, 277V

General specifications



| | |
|--|----------------|
| Product Name | Catalog Number |
| Eaton GHQ thermal magnetic circuit breaker | GHQ1015 |
| | UPC |
| | 782114985106 |
| Product Length/Depth | Product Height |
| 2.63 in | 4 in |
| Product Width | Product Weight |
| 3 in | 0.42 lb |
| Warranty | Certifications |
| 1 year | UL 489 |

Catalog Notes

Includes 4A33462H01 load clip.

Physical Attributes

Circuit breaker type

GHP

Frame size

GDB

Number of poles

Single-pole

Type

Circuit breakers

Performance Ratings

Amperage Rating

15 A

Interrupt rating

14 kAIC

Trip Type

Non-Interchangeable

Voltage rating

277V

Resources

Brochures

[MOEM MCCB Product Selection Guide](#)

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Drawings

[G-frame Molded Case Circuit Breaker Drawing](#)

Specifications and datasheets

[Eaton Specification Sheet - GHQ1015](#)

[Series C G-Frame Time Current Curves](#)

Time/current curves

[Type GHB/GHC/GD/GPS 2 and 3-pole, 15-100A Time Curve](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com
© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)