

Eaton GHQ1020

Catalog Number: GHQ1020

Eaton GHQ thermal magnetic circuit breaker, Thermal-magnetic circuit breaker, 20 A, 14 kAIC, Single-pole, 277 V, Non-Interchangeable, GHP, GDB-Frame, 120/208/240 V Shunt trip



General specifications

Product Name	Catalog Number
Eaton GHQ thermal magnetic circuit breaker	GHQ1020
	UPC
	782114985113
Product Length/Depth	Product Height
2.9 in	2.9 in
Product Width	Product Weight
1 in	0.4 lb
Warranty	Certifications
1 year	UL 489

Catalog Notes

Includes 4A33462H01 load clip.

Physical Attributes

Circuit breaker type

GHP

Frame size

GDB

Number of poles

Single-pole

Shunt trip

120-240V

Type

Thermal-magnetic circuit breaker

Performance Ratings

Amperage Rating

20 A

Interrupt rating

14 kAIC

Trip Type

Non-Interchangeable

Voltage rating

277V

Resources

Brochures

[MOEM MCCB Product Selection Guide](#)

[Loadcenters and Circuit Breakers](#)

Catalogs

[Eaton's Volume 4—Circuit Protection](#)

Drawings

[G-frame Molded Case Circuit Breaker Drawing](#)

Specifications and datasheets

[Series C G-Frame Time Current Curves](#)

[Eaton Specification Sheet - GHQ1020](#)

Time/current curves

[Type GHB/GHC/GD/GPS 2 and 3-pole, 15-100A Time Curve](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](#)