FEATURES:

- Material: Tin Plated CU UL listed for U.S. & Canada.
- Wire connector rated for 35Kv max.
 Class B/C compressed, concentric, and compact copper conductor
- Expanded wire range when installed with dieless NSi compression tool (N12ID).
- Dimensions are for reference only, tolerance is +/- .06".








PROGRAM: SOLIDWORKS **UPDATED:** 4/2022

SALES REV: A

SIZE: B (11x17)







+			COPPER COMPRESSION CONNECTOR TOOL AND DIE CHART (# OF CRIMPS)										
			NSI				GREENLEE		ILSCO	BURNDY	T&B	HUSKIE	
WIRE SIZE	STRIP LENGTH	DIE COLOR	EXPANDED WIRE RANGE W/N12ID	N1240 SERIES	NSI-12	NSI-12	1240 SERIES		ILC-12/ILC-15 SERIES	Y-35. Y750, PAT 750	TBM-15, TBM-14M	EP510C	
#2AWG	15/16"	BROWN	#2AWG-#6AWG	KC12-2 (1)	CD4 (2)	HT41AW (2)	KC12-2 (1)	ILD-4 (2)	KC12-2(1)	U2CRT (1)	15528 (2)	HT41AW (2)	CD4 (2)

