



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

320 SW 28TH ST  
72712-0000, AR Bentonville  
Phone: 479-250-1930  
Fax: 479-250-1931



## GL2N141 2AWG 1/4"STD 2H 5/8"SPC SHRT BRL Cu CMP Lug

*Nsi Industries*

Catalog Number	GL2N141
Manufacturer	Nsi Industries
Description	2 Hole Short Barrel Copper Compression Lug W/ Peep Hole 2 Awg - 1/4" Bolt - 5/8" Mounting Hole Spacing Short Barrel Copper Compression Lugs With Peep Hole Is A Type Of Copper Compression Connector That Is Produced From High Conductivity Copper Tubing. They Are Tin-Plated to Provide Corrosion Resistance and Are Marked With Die Index and Color Coded For Easy Reference. Listed For 35KV Maximum When Properly Installed.
Weight per unit	4.5 (lbs/each)
Product Category	Large Terminals & Connectors

### Features

Cable Size	# 2 AWG (STR)
Material	Copper
Number of Holes	2
Stud Size	1/4
Voltage Rating	600 V
Warranty	1 YEAR

### Material, Color, and Finish

Color	Brown
Finish	Tin Plated

### Dimensions and Weight

Size	L=2.28 - W=.600 - OD=.420 - ID=.310
------	-------------------------------------



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

320 SW 28TH ST  
72712-0000, AR Bentonville  
Phone: 479-250-1930  
Fax: 479-250-1931

## Descriptions

Description	2AWG 1/4"STD 2H 5/8"SPC SHRT BRL CU CMP LUG
extra long description	NSI GL2N-141 CMP Lug Cu Sht 2 AWG 1
Features	2 Hole Short Barrel Copper Compression Lug w/ Peep Hole 2 AWG - 1/4" Bolt - 5/8" Mounting Hole Spacing Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Long Description	2 Hole Short Barrel Copper Compression Lug w/ Peep Hole 2 AWG - 1/4" Bolt - 5/8" Mounting Hole Spacing Short Barrel Copper Compression Lugs with Peep Hole is a type of copper compression connector that is produced from high conductivity copper tubing. They are tin-plated to provide corrosion resistance and are marked with die index and color coded for easy reference. Listed for 35KV maximum when properly installed.
Product Type	CMP Lug Cu SHT 2 Awg 1/4 BLT-5/8 SPC
Special Features	# 2 AWG (STR) - 1/4 Mounting Holes - 5/8 Hole Spacing

## Manufacturer Information

Brand	Nsi Industries
GTIN	00662381338068
Manufacturers Part Number	GL2N-141
UPC	662381338068

## Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Short Barrel - Two Hole

## Packaging

Carton	1
Weight Per each	4.5

## Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
Mounting	1/4 Mounting Holes
standard	UL486A/B, UL467 (8 AWG -3/0 AWG)