
FEATURES:

- Material: Tin Plated CU
- UL listed for U.S. & Canada.
- Wire connector rated for 35Kv max.
 Class B/C compressed, concentric, and compact copper conductor
- Expanded wire range when installed with dieless NSi compression
- Dimensions are for reference only, tolerance is +/- .06".









PROGRAM: SOLIDWORKS **UPDATED:** 4/2022 SALES REV: A

SIZE: B (11x17)





| + | | | COPPER COMPRESSION CONNECTOR TOOL AND DIE CHART (# OF CRIMPS) | | | | | | | | | | |
|-----------|--------------|-----------|---|--------------|---------|------------|-------------|-----------|-------------------------|------------------------|-----------------|------------|---------|
| I | | | NSI | | | | GREENLEE | | ILSCO | BURNDY | T&B | HUSKIE | |
| WIRE SIZE | STRIP LENGTH | DIE COLOR | EXPANDED WIRE RANGE W/N12ID | N1240 SERIES | NSI-12 | NSI-12 | 1240 SERIES | | ILC-12/ILC-15 SERIES | Y-35. Y750, PAT 750 | TBM-15, TBM-14M | EP510C | |
| #4AWG | 13/16" | GRAY | #4AWG-#6AWG | KC12-4 (1) | CD3 (2) | HT41AU (2) | KC12-4 (1) | ILD-3 (2) | KC12-4(1) | U4CRT (1) | 15527-CK (2) | HT41AU (2) | CD3 (2) |

