

# Eaton GLL 10

Catalog Number: GLL 10

Eaton Crouse-Hinds series GLL grounding bushing, Rigid/IMC, Aluminum lug, #3/0-6 AWG, Malleable iron, 105°C temperature rating, Threaded, 4"



## General specifications

<b>Product Name</b>	<b>Catalog Number</b>
Eaton Crouse-Hinds series GLL grounding bushing	GLL 10
	UPC
	784564123107
<b>Product Length/Depth</b>	<b>Product Height</b>
7 in	6.9 in
<b>Product Width</b>	<b>Product Weight</b>
1.4 in	1.1 lb

## Product specifications

### Trade size

4"

### Conduit type

Rigid/IMC

### Lug size

#3/0-6 AWG

### Area classification

Ordinary/Non-Hazardous Locations

### Material

Malleable iron

### Lug material

Aluminum

### Temperature rating

105°C

### Standards type

NEC/CEC

### Thread

Threaded

## Resources

### Catalogs

[Crouse-Hinds series Grounding Bushings - Rigid-IMC catalog page](#)

### Certification reports

[Grounding Bushings - Rigid-IMC Canadian certification](#)

[Grounding Bushings - Rigid-IMC UL certification](#)

### Specifications and datasheets

[Eaton Specification Sheet - GLL 10](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)