



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

500 Rapides Drive
71457-0000, LA Natchitoches
Phone: 318-352-7414
Fax: 318-352-4100



GM40AV 24-Hour Electromechanical, 40A, SPDT/DPDT, Auto-Vo *Intermatic Inc.*

Catalog Number	GM40AV
Manufacturer	Intermatic Inc.
Description	Starter, 1440 Min Time Setting Mode, 2 No/2 NC Contact Form, 15 Min Time Setting, 1440 Min Time Setting, 120 to 208/240/277 V Ac, 40 A, 2 Poles, Screw Box Lug Connection, -40 °F Operating Temperature, +131 °F Operating Temperature, 8.88 X 6.61 X 3 In Size, 0.02 LB
Weight per unit	1.9 (lbs/each)
Product Category	Electromechanical Time Switches

Features

action	1 x DPDT
amperage rating	40
connection	Screw Box Lug
Contact Configuration	2 NO/2 NC
Contact Rating	40 AMP @ 120 - 277 VAC (Resistive NO), 30 AMP @ 120 VAC (Ballast NO), 20 AMP @ 277 VAC (Ballast NO), 15 AMP @ 120 VAC (Tungsten NO), 30 AMP @ 120 - 277 VAC (Resistive NC), 2 AMP @ 120 VAC (Tungsten NC), 10 AMP @ 277 VAC (Ballast NC)
motor power	1 HP @ 120 VAC (16FLA and 90LRA-NO), 2 HP @ 208-277 VAC (12FLA and 52LRA-NO), 1 HP @ 120 VAC (12FLA and 30LRA-NC), 2 HP @ 240 VAC (10FLA and 30LRA-NC)
operating cycles	50000
Poles	2
Timing Range	15 MIN - 24 HR

Descriptions

Description	24-HOUR ELECTROMECHANICAL, 40A, SPDT/DPDT, AUTO-VO
extra long description	INT-MAT GM40AV 40 A, Autovoltage Ge

Manufacturer Information

GTIN	00078275123755
UPC	078275123755

Taxonomies, Classifications, and Categories

Category Description	TIME CLOCKS
Type	Electromechanical Auto-Voltage

Packaging

Carton	1
Weight Per each	1.9



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

500 Rapides Drive
71457-0000, LA Natchitoches
Phone: 318-352-7414
Fax: 318-352-4100

Uses, Certifications, and Standards

Enclosure	NEMA 3R Plastic
environmental conditions	0 - 95 RH Non-Condensing
Mounting	WALL MOUNT
Operating Temperature	-40 to +131 DEG F, -40 to +55 DEG C
standard	cULus Listed #E10694, HVACR