



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



GMQ3210 3-2/10A 300V Ceramic Time Delay In Line Fuse

Bussmann Fuses

Catalog Number	GMQ3210
Manufacturer	Bussmann Fuses
Description	3-2/10A 300V Inline Fuse For HLQ Holder Size Rejecting, Time Delay Fuse
Weight per unit	0.0160 (lbs/each)
Product Category	Small Dimension Fuses

Features

amperage rating	3-2/10 Amp
class	Supplemental
type of indicators	Non-Indicating
Voltage Rating	300 VAC

Dimensions and Weight

Size	0.72 In Diameter X 2.25 In Length
------	-----------------------------------

Descriptions

Description	3-2/10A 300V CERAMIC TIME DELAY IN LINE FUSE
extra long description	EFSE GMQ-3-2/10 BUSS SMALL DIMENSIO
Long Description	3-2/10A 300V Inline Fuse For HLQ Holder Size Rejecting, Time Delay Fuse
Product Type	Buss Small Dimension Fuse Slow Blow
Special Features	Interrupt Rating 10 kA at 300 Vac, Material Ceramic Tube

Manufacturer Information

Brand	Eaton
GTIN	00051712717045
Manufacturers Part Number	GMQ-3-2/10
UPC	051712717045

Taxonomies, Classifications, and Categories

Category Description	Fuses & Fuse Accessories
Type	Electronic, Time Delay, Size-Rejecting, Low Voltage

Packaging

Carton	1
Weight Per each	0.016



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	In-Line Lighting Ballast Protection
Mounting	PANEL
standard	UL 248-14, CSA, CE