

19.5" Low-Profile Support Just for Outdoor Light Fixtures



Comes complete with...

Access panel cover, gasket, installed 3/4" x 1/2" NPT metal grounding bushing and locknut with copper ground wire for fixture installation.

For use with light fixtures exclusively. Accommodates most fixture styles. UV rated plastic for long outdoor life. Four non-chipping colors.

FEATURES AND BENEFITS

- Molded-in color is permanent—unlike painted posts where lawn equipment chips the color off
 - Streamline design...one of our most competitively priced 19.5" Gard-N-Posts
 - Removable 1/2" KO in cover for photocell installation
 - Metal bushing with ground wire for 2- or 3-wire fixtures
 - Resists damage from lawn equipment
- height! When assembling the Extender with GP37 (see J-5) use standard PVC cement.

CATALOG NUMBER	UPC/DCI/NAED MFG #018997	DESCRIPTION	UNIT PKG	STD PKG	DIM A	DIM B	DIM C
GPL19B	77000	Black	1	6	7.125	2.250	19.500
GPL19BR	77001	Bronze	1	6	7.125	2.250	19.500
GPL19G	77002	Green	1	6	7.125	2.250	19.500
GPL19W	77003	White	1	6	7.125	2.250	19.500

PATENTED.

