

# GRC34, Mechanical Ground Rod Clamp, Cable to Rod

By Burndy  
Catalog # [GRC34](#)



Mechanical Ground Rod Clamp, For Cable to Rod, High Strength, 8 AWG (Sol.) - 1/0 AWG (Str.), 3/4" Ground Rod, 3/8" Stud.

## Application

For Joining A Range Of Cable To Copper Clad, Galvanized Steel, And Stainless Steel Ground Rods, Direct Burial Applications In Earth And Concrete

## General

EU RoHS Indicator	Yes
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GRC, High Strength
UPC	781810230985
UPC 12 Digit	7818102309855

## Dimensions

Dimension - B Length inch	0.65 in
Dimension - Height inch	2.40 in
Dimension - Length Side B inch	0.65 in
Dimension - Width inch	1.09 in
Dimension - Width mm	28 mm

## Conductor Related

Conductor - Copper Solid Size Range	8 AWG
Conductor - Copper Str Size Range	8 AWG - 1/0 AWG
Conductor - Rod Size	3/4 in
Conductor Size	#8 AWG Sol - 1/0 AWG Str
Conductor Type	<ul style="list-style-type: none"> <li>• Rod-Size</li> <li>• CU C Solid-Size</li> </ul>

## Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

## Logistics

Carton Quantity	100
Minimum Pack Quantity	1
Pallet Quantity	27500

## Product Assets

[3D Models - GRC34\\_MODEL-IGES](#)  
[3D Models - GRC34\\_MODEL-STEP](#)  
[3D Models - GRC34\\_MODEL-PDF](#)  
[Customer Notices - Prop 65 Notice](#)  
[Sales Drawings - SA..076868-01](#)