



SKU: GSW-21

UPC: 0032076890216

Features & Benefits:

Description: Maintained Contact Push-Button Switch-Motor Rated, Single Pole-Single Throw, Push On-Push Off, 10 A/125 V AC, 8 A/125 V, 4 A/250 V, 1/3 HP 125 V AC, Wire Leads, Black Finish, 1/Pkg

Specs

Dimensions

Lead Length	6 in
-------------	------

Additional Class Attributes

Control Style	Single Pole
Illuminated	No
Mounting Method	Recessed
Number of Positions	2
Speeds	1
Switch Outlet Grade	Commercial
Switch Style	Standard
Switch Type	Push Button
Warranty	1 Year
Wattage	2500

Material and Finish

Material	Nickel
----------	--------

Additional Technical Specifications

Connector Amperage Rating CU (Derated where applicable)	10 Amps
Contact Arrangement	SPST
Contact Type	Maintained
Terminal Type	Wire leads

Testing Standards

Prop65 Compliance	WARNING: Cancer and Reproductive Harm - www.P65warnings.ca.gov
-------------------	--

Color

Color	Chrome
-------	--------

Voltage

Maximum Voltage	250 V
Minimum Voltage	125 V

Environment and Temperature

Environmental Conditions	Indoor
--------------------------	--------

General

Bag Quantity	1
Carton Quantity Description	STD PACK QTY 5
UPC Code	03207689021